


Rev	AWO #	Description	Date	Appr
-		RELEASED	1/11/05	
A		REVISED DIM.	11/22/12	
B		REDRAWN	6/30/14	HR/QZL

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Contact: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max initial

Mechanical:

Recommended wire range: 24–28 AWG

Temperature Rating:

Operating temperature: –55°C to +105°C


Packaging:

B = Loose Cut

R = Tape and Reel

Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB SOCKET CONTACT, 24-28 AWG

GOLD FLASH

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				HOLE			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015	.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS	1/11/05		CHECKED			
APPROVED							
SIZE				PART NO.			
X				DCS-01-X			
REF: S00087				SCALE: NTS			
				SHEET 1 OF 1			