






APPROVED: _____
DATE: _____ TITLE: _____

3	2	1
Rev	WVO #	Description
-		Released
A		Updated
		Date
		6/11/03
		5/31/12
		Appr



* SHINY, SMOOTH SURFACE

* MATTE, TEXTURED SURFACE



NOTE: * INDICATES CRITICAL POINTS

SPECIFICATIONS:

Material:

Hood: Aluminum Die Cast

Hardware: Copper Alloy

Finish:

Hood: Aluminum

Hardware: Nickel Plated

Packaging:

Two(2) of each part shown is packaged in a plastic bag.

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES HOLES
X ± .10 ØX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS

DRAWN	SLS	6/11/03
CHECKED		
APPROVED		

ADAM TECH

909 Rohway Avenue, Union, NJ 07083
Phone: 908-687-1600 Fax: 908-687-8599

TITLE

HOOD, D-SUB, 9 POS, ALUMINUM DIE CAST,
SHORT SCREW, 10.0mm ENTRY HOLE

SIZE	PART NO.	REV.
X	DE09-HDLB-AL-SS-394	A
REF:	SCALE: NTS	SHEET 1 OF 1