

6

5

4

3

2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/8/14	

APPROVED: _____



DATE: _____ TITLE: _____

D


D

C

C



RECOMMENDED PANEL CUT



B

B

A

A

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Electrical:

Operating voltage: 600 VAC max

Current rating: 11 Amps max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 5,000 VAC for 1 minute

Mechanical

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

6.35MM PITCH CONNECTOR, SINGLE ROW

HOUSING, MALE, 6 POSITION

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES							
.X	± .10	ØX	± .10	HOLE5			
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	AY		5/8/14				
CHECKED	CH		5/8/14				
APPROVED							
SIZE		PART NO.					
X		DME-M-06					
REF:		S00123T					
		SCALE: NTS					
		SHEET 1 OF 1					