

6

5

4

3


2

1


Rev	AWO #	Description	Date	Appr
-		RELEASED	08/30/12	

APPROVED: _____

DATE: _____ TITLE: _____



Panel hole dimensions [4.80]



SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL94V-0

Insulator color: Natural

Electrical:

Current rating: 11A

Voltage rating: 600V

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 5000 VAC for 1 minut

Temperature range: -55°C to +105°C

Environmental:

Lead free, RoHS compliant.

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: 6.35MM PITCH CONNECTOR, SINGLE ROW
HOUSING, MALE, 8 POSITION

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED							
INCHES				Holes			
.X	± .10	ØX	± .10				
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN	TW		08/30/12				
CHECKED	AV		08/30/12				
APPROVED							
SIZE				PART NO.			
X				DME-M-08			
REF: S00123T				SCALE: NTS			
				SHEET 1 OF 1			