

6

5

4

3





2

1


APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/20	




06P



15P



09P



12P

PRODUCT VIEW

Poles	Dimensions				
	A	B	C	D	E
06	.250 [6.35]	.550 [13.97]	.800 [20.32]	.094 [27.80]	1.091 [27.70]
09	.500 [12.70]	.807 [20.50]	.807 [20.50]	1.110 [28.20]	1.106 [28.10]
12	.750 [19.05]	1.067 [27.10]	.807 [20.50]	1.110 [28.20]	1.106 [28.10]
15	1.000 [25.40]	1.343 [34.10]	.811 [20.60]	1.114 [28.30]	1.122 [28.50]

SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-2

Insulator color: Natural

Electrical:

Current rating: 06~15P: 9 Amp Max (With UL1007, 16AWG)

Contact resistance: 20 mohms max

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 2,900 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	LH	2/21/20
CHECKED	AY1	2/21/20
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

.250 [6.35MM] PITCH CONNECTOR, 06~15 POS
HOUSINGS, MALE, VERTICAL

SIZE X	PART NO. DME-M2-XX-SQ	REV. -
REF: S00124T	SCALE: NTS	SHEET 1 OF 1