





6 5 4 3 2 1

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/20/19	



SPECIFICATIONS:

Material:

Contacts: Brass, Tin Plated, Thickness: 0.3mm

Electrical:

Voltage rating: 600 VAC/DC

Current rating: 2~5 Circuit 12 A AC/DC

6~15 Circuit 9 A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 2900 VAC For 1 Minute

Mechanical:

Wire: A: AWG# 18~22


B: AWG# 16~20

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	LH	6/20/19
CHECKED	TY	6/20/19
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
CRIMP CONTACT, DME SERIES
TIN PLATED

SIZE	PART NO.	REV.
X	DME-X2-C-F-R	-
REF:	S00124T	SCALE: NTS
SHEET 1 OF 1		