







Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/20	

APPROVED: _____

DATE: _____ TITLE: _____



6 POSITION

9 POSITION

12 POSITION

15 POSITION

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Electrical:

Current rating: 06~15P: 9 Amp Max (With UL1007, 16AWG)

Contact resistance: 20 mohms max

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 2,900 VAC for 1 minute

Temperature Rating:

Temperature Rating:
-40°C to +105°C

Environmental:

Lead free, RoHS compliant.


$$A = .250 [6.35] \times \text{No. of Spaces}$$

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010		ADAM INTERCONNECTS		909 Rahway Avenue,	
				Union, NJ 07083	
				Phone: 908-687-5000	
				Fax: 908-687-5710	
APPROVALS		DATE		TITLE WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITHOUT POLARIZING PEG, FEMALE PIN	
DRAWN	LH	2/21/20			
CHECKED	AY1	2/21/20			
APPROVED					
		SIZE X	PART NO. DME-F-XX-S2-SQ	REV -	
		REF: S00124T	SCALE: NTS	SHEET 1 OF 1	