





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/22/10	
A		REDRAWN	08/30/12	



Panel hole dimensions



SPECIFICATIONS:

Material:
Insulator: Nylon66, rated UL94V-2
Insulator color: Natural
Electrical:
Current rating: 13A
Voltage rating: 600V
Insulation resistance: 1000 Mohms min
Dielectric withstanding voltage: 5000 VAC for 1 minut
Temperature range: -55°C to +105°C
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

6.35MM PITCH CONNECTOR, SINGLE ROW
HOUSING, MALE, 4 POSITION

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				HOLES			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	DY		11/22/10	SIZE	PART NO.		REV.
CHECKED				X	DME-M-04		A
APPROVED				REF:	S00123T	SCALE: NTS	SHEET 1 OF 1