





Rev	AWO #	Description	Date	Appr
-		RELEASED	10/02/12	

APPROVED: _____

DATE: _____ TITLE: _____



Panel hole dimensions



SPECIFICATIONS:

Material: Nylon66, rated UL 94V-2
Insulator color: Natural
Electrical:
Voltage Rating: 600V Max.
Current rating: 11 Amps Max.
Insulation resistance: 1,000M ohms min
Dielectric withstanding voltage: 5,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Environmental:
Lead free, RoHS compliant.

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.250 [6.35MM] PITCH CONNECTOR, 6 POS
HOUSINGS, MALE, VERTICAL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	TW	10/02/12		SIZE	PART NO.	DME-M-06-SQ	REV.
CHECKED	AV	10/02/12		X			-
APPROVED				REF:	S00123T	SCALE: NTS	SHEET 1 OF 2

