





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/02/12	
A		UPDATE DIM.	3/14/18	AY/DH
B		UPDATE DIM.	7/15/21	LH/RL



Panel hole dimensions



SPECIFICATIONS:

Material:
Insulator: Nylon66, rated UL 94V-2
Insulator color: Natural
Electrical:
Voltage Rating: 600V Max.
Current rating: 11 Amps Max.
Insulation resistance: 1,000M ohms min
Dielectric withstanding voltage: 5,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	Ø.X ±.10
.XX ±.020	Ø.XX ±.015
.XXX ±.015	Ø.XXX ±.010

DRAWN	TW	10/02/12
CHECKED	AY	10/02/12
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.<250 [6.35MM] PITCH CONNECTOR, 9 POS
HOUSINGS, MALE, VERTICAL

SIZE X	PART NO. DME-M-09-SQ	REV. B
REF: S00123T	SCALE: NTS	SHEET 1 OF 1