


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/26/10	
A		ADDED DIM.	10/27/17	AY/NC



RECOMMENDED PCB LAYOUT

Positions: 2 thru 10

A = .250 [6.35] No. of Positions + .050 [1.27]

B = .250 [6.35] No. of Spaces

C = .250 [6.35] No. of Positions + .330 [8.38]

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contact: Phosphor Bronze, Tin plated

Electrical:

Voltage rating: 600 VAC

Current rating: 13 Amp (2~4P), 11 Amp (6~10P).

Dielectric withstanding voltage: 5000 VAC for 1 minute

Temperature Rating:

-55°C to +105°C

Environmental:

Lead free, RoHS compliant.

RoHS
COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN

DY

10/26/10

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

WIRE TO BOARD HEADER, MALE WITH EARS
6.35MM, RIGHT ANGLE

DME-M-XX-RA-E

REV.
-

REF: S00123T

SCALE: NTS

SHEET 1 OF 1