





APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	6/19/19	



SECTION A-A



SECTION B-B



SPECIFICATIONS:

Material:

Contacts: Brass, Tin Plated, Thickness: 0.3mm

Electrical:

Voltage rating: 600 VAC/DC

Current rating: 2~5 Circuit 12 A AC/DC

6~15 Circuit 9 A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 2900 VAC For 1 Minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



PART #	WIRE AWG	DIMENSIONS				
		C	D	E	F	G
DME-A2-C-M-R	18 ~ 22	.134 [3.40]	.134 [3.40]	.094 [2.40]	.094 [2.40]	.429 [10.90]
DME-B2-C-M-R	16 ~ 20	.177 [4.50]	.177 [4.50]	.114 [2.90]	.138 [3.50]	
DME-C2-C-M-R	12 ~ 14	.264 [6.70]	.228 [5.80]	.130 [3.30]	.161 [4.10]	.618 [15.70]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 Ø.X ± .10
 .XX ± .020 Ø.XX ± .015
 .XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	LH	6/19/19
CHECKED	TY	6/19/19
APPROVED		

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		CRIMP CONTACT, DME SERIES TIN PLATED		
SIZE	PART NO.	REV.		
X	DME-X2-C-M-R	-		
REF:	S00124T	SCALE:	NTS	SHEET 1 OF 1