


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/20	



Poles	Dimensions			
	A		B	
02	.250	[6.35]	.550	[13.97]
03	.500	[12.70]	.800	[20.32]
04	.750	[19.05]	1.050	[26.67]
05	1.000	[25.40]	1.300	[33.02]
06	1.250	[31.75]	1.550	[39.37]
07	1.562	[38.10]	1.800	[45.72]
08	1.750	[44.45]	2.050	[52.07]
09	2.000	[50.80]	2.300	[58.42]
10	2.250	[57.15]	2.550	[64.77]

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Electrical:

A Current rating: 02~10P: 12 Amp Max (With UL1015, 12AWG)

Contact resistance: 20 mohms max

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 2,900 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

INCHES		MILL	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS

DRAWN	LH	2/21/2
-------	----	--------

CHECKED	AY1	2/21/2
---------	-----	--------

APPROVED		
----------	--	--

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITHOUT POLARIZING PEG. MALE PIN
-------	--

SIZE X	PART NO. DME-XX-S2-S	REV -
-----------	-------------------------	----------

REF:	S00124T	SCALE:	NTS	SHEET	1	OF	1
------	---------	--------	-----	-------	---	----	---