

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date

Appr

-

RELEASED

2/21/20

D




D

C


C

B

B




.550 [13.97]




.250 [6.35]

6 POSITION




.800 [20.32]




.500 [12.70]

9 POSITION




1.050 [26.67]




.750 [19.05]

12 POSITION



1.300 [33.02]



1.00 [25.40]

15 POSITION

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Contacts: Phosphor Bronze, Tin plated

Electrical:

Current rating: 06~15P: 9 Amp Max (With UL1007, 16AWG)

Contact resistance: 20 mohms max

Insulation resistance: 1,000M ohms min

Dielectric withstanding voltage: 2,900 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.



A = .250 [6.35] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS

DATE

DRAWN

LH

2/21/20

CHECKED

AY1

2/21/20

APPROVED

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITHOUT
POLARIZING PEG, MALE PIN

SIZE
X

PART NO.

DME-XX-S2-SQ

REV.

-

REF:

S00124T

SCALE:

NTS

SHEET 1 OF 1

A

6

5

4

3

2

1