



APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	3/6/20	
A		UPDATE DIM.	7/30/20	LH/TL



Section B-B



Section A-A



SPECIFICATIONS:

Material:

Contact: Phosphor Bronze, Tin Plated

Thickness: 0.2mm

Electrical:

Voltage rating: 250 V AC/DC

Current rating: 20 Awg: 5 Amps max

22 Awg: 5 Amps max

24 Awg: 4 Amps max

26 Awg: 3 Amps max

28 Awg: 2 Amps max

30 Awg: 1 Amp max

Contact resistance: 10 mohms max.

Dielectric withstanding voltage: 1500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



P/N	Wire size	Dim. A	Dim. B	Dim. C	Dim. D
DMT-A5-C-F-T-R	#26~#30AWG	.071 [1.80]	.063 [1.60]	.094 [2.40]	.075 [1.90]
DMT-B5-C-F-T-R	#20~#24AWG	.083 [2.10]	.083 [2.10]	.106 [2.70]	.098 [2.50]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS DATE

DRAWN	LH	3/6/20
CHECKED	AY1	3/6/20
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.118" [3.0mm] CRIMP TERMINAL,
TIN PLATED, ON REEL

SIZE X	PART NO. DMT-X5-C-F-T-R	REV. A
REF: S00015T	SCALE: NTS	SHEET 1 OF 1