

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/6/20	



Positions: 02 thru 24

A= .118 [3.00] x No. of Space

B= .118 [3.00] x No. of Space + .157 [4.00]

SPECIFICATIONS:

Material:

Insulator: Glass-Filled Polyimide, rated UL 94V-0

Insulator color: Black

Electrical:

Voltage rating: 250 V AC/DC

Current rating: 5 A AC/DC

Contact resistance: 10 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 1500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010				ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE		TITLE .118" [3.00mm] CRIMP HOUSING, SINGLE ROW LATCHING TYPE, HALOGEN-FREE			
DRAWN	LH	3/6/20		SIZE X	PART NO. DMT-D-1-XX		REV. -
CHECKED	AY1	3/6/20		REF: S00015T		SCALE: NTS	SHEET 1 OF 1
APPROVED							

6

5

4

3

2

1