





Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/19	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



B | SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator Color: Black

Contact: Copper Alloy

Shell: Brass, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area,

Tin over Nickel underplate on solder area

Electrical:

Voltage: 40 VAC(RMS) max

Current rating: 0.5 Amps per Contact

Contact resistance: 30 mohms max

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 500 VAC(RMS)

Temperature Rating:

Operating temperature: -55°C to $+85^{\circ}\text{C}$

Environmetal:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

INCHES	TOLERANCE	MILLIMETERS	TOLERANCE
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	AY	2/21/19
CHECKED	LW	2/21/19
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	DISPLAYPORT RECEPTACLE, VERTICAL, SINGLE PORT, 20 PIN, SEL GOLD PLATED
-------	---

SIZE X	PART NO. DPC-F-S-VT-CS1	REV. -
-----------	----------------------------	-----------

REF:	S00027T	SCALE:	NTS	SHEET	1	OF	1
------	---------	--------	-----	-------	---	----	---