







APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/7/16	
A		ADDED DIM.	1/30/18	AY/DH
B		ADDED DRAWING	1/25/19	AY/RC1
C		UPDATE DRAWING	5/4/20	LH/DH



Pin No.	Signal Type	Pin No.	Signal Type
1	Out	11	GND
2	GND	12	Out
3	Out	13	CONFIG
4	Out	14	CONFIG
5	GND	15	I/O
6	Out	16	GND
7	Out	17	I/O
8	GND	18	In
9	Out	19	PWR RTN
10	Out	20	PWR Out



SPECIFICATIONS:

Material:
 Housing: Hi-temp thermoplastic, rated UL 94V-0, Color: Black
 Contact: Phosphor Bronze
 Shell: Brass, Nickel plated
 Spring: Stainless Steel

Plating:
 Gold flash over Nickel underplate on contact area,
 Tin over Nickel underplate on solder tails

Electrical:
 Operating voltage: 40 VAC max
 Current rating: 0.5 Amp per Contact
 Contact Resistance: 30 mohms max
 Insulation Resistance: 100 Mohms min.
 Withstanding Voltage: 500 VDC

Temperature Rating:
 Operating temperature: -20°C to +85°C

Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

ADAM TECH INTERCONNECTS
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	AY	7/7/16
CHECKED	TW	7/7/16
APPROVED		

TITLE		
DISPLAYPORT PLUG, MOLDING TYPE, MEAN LATCH WITH SHELL LOCK, SEL GOLD PLATED		
SIZE	PART NO.	REV.
X	DPC-M-SD-M2-L	C
REF: S00078T	SCALE: NTS	SHEET 1 OF 2

6

5

4

3

2

1


APPROVED: _____

DATE: _____ TITLE: _____






Rev	AWO #	Description	Date	Appr
-----	-------	-------------	------	------

SEE SHT 1 OF 2 FOR REVISION

Top Cover



Bottom Cover



SPECIFICATIONS:

Material:
 Top Cover: Nylon66, rated UL 94V-2, Color: Black
 Bottom Cover: Nylon66, rated UL 94V-2, Color: Black

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 Ø.X ± .10
 .XX ± .020 Ø.XX ± .015
 .XXX ± .015 Ø.XXX ± .010

ADAM TECH
 INTERCONNECTS
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	AY	7/7/16
CHECKED	TW	7/7/16
APPROVED		

TITLE DISPLAYPORT PLUG, MOLDING TYPE, MEAN LATCH WITH SHELL LOCK, SEL GOLD PLATED		
SIZE X	PART NO. DPC-M-SD-M2-L	REV. C
REF: S00078T	SCALE: NTS	SHEET 2 OF 2

6

5

4

3

2

1