

6

5

4

3








2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/10/08	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Hood: Polyester

Hardware: Copper Alloy

Finish:

Hood: Bright Chrome Plated Plastic

Hardware: Nickel Plated

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

D-SUB HOOD, 15P, GROMMET TREE, BRIGHT

CHROME PLATED PLASTIC, THUMB SCREW

PART NO.

DA15-HD-PN-TS

REV.

-

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES	HILES		
.X ± .10	ØXX ± .10		
.XX ± .020	ØXXX ± .015		
.XXX ± .015	ØXXXX ± .010		
APPROVALS		DATE	
DRAWN	DY	6/10/08	
CHECKED			
APPROVED			

SIZE	PART NO.	REV.
X	DA15-HD-PN-TS	-
SCALE:	NTS	SHEET 1 OF 1