





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/15/05	
A		CHART UPDATE	4/21/06	
B		UPDATED DRAWING	11/13/14	AY/LL
C		UPDATED DIM.	2/21/18	AY/MY



SPECIFICATIONS:

Material:

Insulator: Thermoplastic, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Shell: Steel, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area,

Electrical:

Contact resistance: 10 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +125°C

Environmental:

Lead free, RoHS compliant



DXXX	NO. OF CONTACTS	DIMENSIONS				
		A	B	C	D	E
DE09	9	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.759 [19.28]	.436 [11.08]
DA15	15	.994 [25.25]	1.312 [33.32]	1.541 [39.14]	1.083 [27.51]	.763 [19.39]
DB25	25	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.625 [41.28]	1.309 [33.24]
DC37	37	2.182 [55.42]	2.500 [63.50]	2.729 [69.32]	2.272 [57.71]	1.963 [49.86]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	4/15/05
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
D-SUB PLUG, STANDARD PROFILE
WIRE WRAP TAIL

SIZE X	PART NO. DXXX-PT-2	REV. C
REF: S00019T	SCALE: NTS	SHEET 1 OF 1