










APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/14/05	
A		ADDED THREAD LENGTH	1/24/11	
B		ADDED CABLE ENTRY DIA	2/3/11	
C		ADDED DIM.	6/29/16	AY/IC
D		CORRECTED HOOD MATERIAL	1/21/26	SS



DXXX	DIMENSIONS					
	A	B	C	D	ØE	F
DE09	1.220 [31.00]	.614 [15.60]	1.850 [47.00]	.980 [24.90]	.275 [7.00]	.559 [14.20]
DA15	1.575 [40.00]	.630 [16.00]	1.898 [48.20]	1.307 [33.20]	.389 [9.90]	.756 [19.20]
DB25	2.098 [53.30]	.630 [16.00]	1.917 [48.70]	1.850 [47.00]	.393 [10.00]	1.047 [26.60]
DC37	2.717 [69.00]	.638 [16.20]	1.913 [48.60]	2.500 [63.50]	.551 [14.00]	1.047 [26.60]

SPECIFICATIONS:

Material:

Hood: Zinc Alloy Die Cast

Finish: Chromate plated

Hardware: Copper Alloy, Nickel plated

Environmental:

Lead free, RoHS compliant

Agency Certifications:

cUL, Adam Tech file #E224053



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	6/14/05
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
D-SUB HOOD, ZINC ALLOY DIE CAST,
THUMB SCREWS

SIZE X	PART NO. DXXX-HD-AL-TS	REV. D
REF:	SCALE: NTS	SHEET 1 OF 1