





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/14/07	
A		REDRAW	9/14/11	



Recommended PCB Layout



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Copper alloy

Shell: SPCC

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant

DXXX	NO. OF CONTACTS	DIMENSIONS			
		A	B	C	D
DE09	9	1.213 [30.81]	.984 [24.99]	.666 [16.92]	.436 [11.08]
DA15	15	1.541 [39.14]	1.312 [33.32]	1.004 [25.50]	.763 [19.39]
DB25	25	2.088 [53.04]	1.852 [47.04]	1.534 [38.96]	1.309 [33.24]
DC37	37	2.729 [69.32]	2.500 [63.50]	2.182 [55.42]	1.963 [49.86]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
D-SUB PLUG, FLUSH MOUNT
STRAIGHT PCB TAIL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 .XX ± .020 .XXX ± .015 APPROVALS DATE DRAWN SS 2/14/07 CHECKED APPROVED		SIZE X PART NO. DXXX-PA-M1 REV. A	
REF: S00087T		SCALE: NTS SHEET 1 OF 1	

