




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/28/05	
A		REDRAWN	01/28/13	
B		REVISED DIM.	2/26/14	AY

APPROVED: _____

DATE: _____ TITLE: _____



DXXX	NO. OF CONTACTS	DIMENSIONS		
		A	B	C
DE09	9	.666 [16.92]	.984 [24.99]	1.213 [30.81]
DA15	15	.994 [25.25]	1.312 [33.32]	1.541 [39.14]
DB25	25	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]
DC37	37	2.182 [55.42]	2.500 [63.50]	2.729 [69.32]

SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Steel, Tin plated

Hardware: Brass, Nickel plated

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

D-SUB PLUG, SOLDER CUP
RIVETED #4-40 CLINCH NUTS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		INCHES		HOLES	
.X	± .10	ØX	± .10	.X	± .10
.XX	± .020	ØXX	± .015	.XX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .010
APPROVALS		DATE			
DRAWN	SS	4/28/05			
CHECKED					
APPROVED					
SIZE		PART NO.		REV.	
X		DXXX-PD-SL		B	
REF:		S00087T		SCALE: NTS	
				SHEET 1 OF 1	

ROHS
COMPLIANT