





Rev	AWO #	Description	Date	Appr
-		RELEASED	4/15/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Steel, Tin plated

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant



Positions	DIMENSIONS			
	A	B	C	D
9	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]
15	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]
25	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]
37	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]

Unit: Inch / mm

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: D-SUB SOCKET, STRAIGHT PCB TAIL

HIGH PROFILE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				DRAWN: SS				DATE: 4/15/05			
INCHES				Holes				CHECKED:			
.X ± .10				ØX ± .10				APPROVED:			
.XX ± .020				ØXX ± .015				SIZE: X			
.XXX ± .015				ØXXX ± .010				PART NO.: DXXX-SE-1			
APPROVALS:				DATE:				REV: -			
DRAWN:				SS				SCALE: NTS			
CHECKED:								SHEET 1 OF 1			
APPROVED:											