





Rev	AWO #	Description	Date	Appr
-		RELEASED	4/22/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Steel, Tin plated

Hardware: Brass, Nickel plated

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant

Recommended soldering temp: 235°C for 5 seconds

DXXX	NO. OF CONTACTS	DIMENSIONS		
		A	B	C
DE09	9	.643 [16.33]	.984 [24.99]	1.213 [30.81]
DB25	25	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.197 [5.00] SLIMLINE D-SUB SOCKET
FORKED BOARDLOCKS, #4-40 INSERTS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		TITLE .197 [5.00] SLIMLINE D-SUB SOCKET FORKED BOARDLOCKS, #4-40 INSERTS	
INCHES	HOLES	SIZE	PART NO.
.X ±.10	ØX ±.10	X	DXXX-SN-24
.XX ±.020	ØXX ±.015		
.XXX ±.015	ØXXX ±.010		
APPROVALS	DATE	SCALE: NTS	SHEET 1 OF 1
DRAWN SS	4/22/05		
CHECKED			
APPROVED			