



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/29/05	
A		REDRAW	8/15/11	



SPECIFICATIONS:

Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Shell: SPC
Hardware: Brass, Nickel plated
Plating:
Gold flash over Nickel underplate overall
Electrical:
Operating voltage: 250 VAC max
Current rating: 5 Amps max
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -65°C to +125°C
Environmental:
Lead free, RoHS compliant

DXXX	NO. OF CONTACTS	DIMENSIONS					
		A	B	D	E	F	
DE09	9	1.213 [30.81]	.984 [24.99]	.643 [16.33]	.436 [11.08]	.756 [19.20]	
DA15	15	1.541 [39.14]	1.312 [33.32]	.971 [24.66]	.763 [19.39]	1.091 [27.70]	
DB25	25	2.088 [53.04]	1.852 [47.04]	1.511 [38.38]	1.309 [33.24]	1.618 [41.10]	
DC37	37	2.729 [69.32]	2.500 [63.50]	2.159 [54.84]	1.963 [49.86]	2.256 [57.30]	

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES
.X ± .10 ØX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS

DRAWN	SS	4/29/05
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
D-SUB SOCKET, CRIMP AND POKE
RIVETED #4-40 CLINCH NUTS

SIZE	PART NO.	DXXX-SR-SL	REV.
X			A
REF: S00087T	SCALE: NTS	SHEET 1 OF 1	