






APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:
Insulator: Hi-Temp Thermoplastic, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Metal Shell: SPCC, Nickel plated
Board Lock: Brass, Tin plated
Screw & Nut: Brass, Nickel plated
Plating:
Gold over Nickel underplate on contact area,
Tin over Nickel underplate on solder tails.
Electrical:
Operating voltage: 300 VAC max
Current rating: 5 Amps max
Contact resistance: 13 mohms max.
Insulation resistance: 1000 Mohms min
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Environmental:
Lead free, RoHS compliant.

Rev	AWO #	Description	Date	Appr
-		RELEASED	06/29/05	
A		UPDATE SHAPE	9/25/14	HRLW



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

D-SUB, 25 POS FEMALE, RIGHT ANGLE, SMT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015	.XX	± .015	ØXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE				DATE			
DRAWN	SS			06/29/05							
CHECKED											
APPROVED											
SIZE				PART NO.				REV.			
X				DB25-SS-24				A			
REF: S000037				SCALE: NTS				SHEET 1 OF 1			