



Rev	AWO #	Description	Date	Appr
-		RELEASED	05/10/12	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SECTION A-A

Positions: 02 thru 24
A = .197 [5.00] x No. of Positions
B = .197 [5.00] x No. of Spaces

	Dim A	Dim B
2-6P	±.006 [0.15]	±.004 [0.10]
7-12P	±.008 [0.20]	±.008 [0.20]
13-18P	±.012 [0.30]	±.010 [0.25]
19-24P	±.016 [0.40]	±.012 [0.30]

SPECIFICATIONS:

Material:
Insulator: PA66, rated UL 94V-0
Insulator color: Green
Wire guard: Stainless Steel
Contact: Brass, Tin plated
Screw: Steel, M2.6/Zn Plated
Electrical:
Operation voltage: 300 VAC
Current rating: 10 Amps
Withstanding Voltage: 1.6KV
Mechanical:
Solid wire (AWG): 12-26
Stranded wire (AWG): 12-26
Torque(lb-in): 3.5
Wire strip length (mm): 5-6
Temperature Rating:
Operating temperature: -40°C to +115°C
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

EURO BLOCK, .197 [5.00] PITCH

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH			
.X ± .10 ØX ±.10 .XX ± .020 ØXX ±.015 .XXX ± .015 ØXXX ±.010				909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
APPROVALS		DATE		TITLE			
DRAWN	TW	05/10/12		EURO BLOCK, .197 [5.00] PITCH			
CHECKED	AY	05/10/12		VERTICAL			
APPROVED				SIZE		PART NO.	
				X		EB133-XX-C	
REF.	SCALE		NTS	SHEET		1 OF 1	
	S00007T						