





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/1/16	
A		UPDATE DRAWING	9/30/20	AY/DH



RECOMMENDED PCB LAYOUT



Positions: 02 thru 24

A = .135 [3.50] x No. of Spaces + .165 [4.20]

B = .135 [3.50] x No. of Spaces

SPECIFICATIONS:

Material:

Insulator: LCP, rated UL 94V-0

Insulator color: Black

Contact: Copper Alloy, Tin plated

Electrical:

Voltage rating: 300V

Current rating: 10 A

Withstanding Voltage: 1600 V/1 Min

Mechanical:

Wire range: 24-16 AWG

Stripping length: 7~8mm

Temperature Rating:

Operating temperature: -40°C to +130°C

ENVIRONMENTAL:

Lead free, rohs compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010				
APPROVALS		DATE		TITLE EURO BLOCK, .135 [3.50] PITCH
DRAWN	AY	6/2/16		
CHECKED	AT	6/2/16		
APPROVED				
SIZE X		PART NO. EB142A-XX-A-180		REV. A
REF: S00067C		SCALE: NTS		SHEET 1 OF 1