

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/25/14	

6

5

4

3



2

1


APPROVED: _____

DATE: _____ TITLE: _____

D



C



SECTION A-A

B

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Screw: Steel, M3.0/Zinc plated

Cage: Brass, Nickel plated

Pin Header: Brass, Tin plated

Electrical:

Voltage rated: 300 VAC

Current rated: 16 Amps

Contact resistance: 20 mΩ

Insulation resistance: 500 MΩ @ 500 VDC

Withstanding voltage: 2000V AC/1 Min

Mechanical:

Solid wire: 26-12AWG 2.5mm²

Torque (Lb-in): 0.5Nm (4.5lb-in)

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.

A

Positions: 02 thru 24
A = .295 [7.50] x No. of Positions
B = .295 [7.50] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES
.X ± .10 ØXX ± .10
.XX ± .020 ØXXX ± .015
.XXX ± .015 ØXXX ± .010

TITLE

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

EURO BLOCK, .295 [7.50] PITCH

APPROVALS		DATE	
DRAWN	AY	8/25/14	
CHECKED	SC	8/25/14	
APPROVED			
SIZE		PART NO.	
X		EB147A-XX-M	
REV.		-	
REF:		S00067C	
SCALE:		NTS	
SHEET		1 OF 1	

A

B

C

D

6

5

4

3

2

1

