

6

5

4

3



2

1




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



RECOMMENDED PCB LAYOUT



WITHOUT COVER

SPECIFICATIONS:

Material:

Insulator: PA, rated UL 94V-0

Insulator color: Green

Contact: Copper Alloy

Electrical:

Voltage rating: 300V

Current rating: 10A

Dielectric withstanding voltage: 1,600 VAC for 1 minute

Mechanical:

Strip length: 8~9mm

Wire Range: 24~16 AWG

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 01 thru XX

A= .138 [3.50] x No. of Positions + .055 [1.40]

B= .138 [3.50] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

EURO BLOCK, .138 [3.50] PITCH, HORIZONTAL

SIZE
X

PART NO.

EB163A-XX-A

REV.
-

REF: S00067C

SCALE: NTS

SHEET 1 OF 1