

6

5

4

3




2

1


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/22/21	



RECOMMENDED PCB LAYOUT

**SPECIFICATIONS:****Material:**

Insulator: PA, rated UL 94V-0

Insulator color: Green

Pin Header: Copper Alloy, Tin plated

Electrical:

Voltage rating: 600 V

Current rating: 51 A

Dielectric withstanding voltage: 2,200 V for 1 minute

Mechanical:

Wire range: 18~4AWG

Wire strip length: 17~18mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 18

A= .591 [15.00] x No. of Space + .449 [11.40]

B= .591 [15.00] x No. of Space

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS

DATE

DRAWN

LH

2/22/21

CHECKED

NL

2/22/21

APPROVED

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.591[15.00] PITCH SPRING CLAMP
TERMINAL BLOCKS, RIGHT ANGLE

SIZE

PART NO.

X

EB171A-XX-K

REV.

-

REF: S00067C

SCALE: NTS

SHEET 1 OF 1