

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description





Date

Appr

-

RELEASED

7/18/19



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: PPA, Glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze, Tin Plated

Electrical:

Voltage rating: 150 V

Current rating: 6 Amp

Dielectric withstanding voltage: 2000 VAC for 1 minute

Mechanical:

Strip length: 5.0-6.0mm

Wire Range: 24-20 AWG,

Temperature Rating:

-60°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 12

A = .098 [2.50] x No. of Positions + .020 [0.50]

B = .098 [2.50] x No. of Space

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS DATE

DRAWN LH 7/18/19

CHECKED IL 7/18/19

APPROVED

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
SPRING CLAMP EURO BLOCK, .098 [2.50] PITCH
RIGHT ANGLE, SMT TYPE

SIZE X	PART NO. EB176-A-XX-V-RA-TSMT	REV. -
-----------	----------------------------------	-----------

REF: S00046C	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------

6

5

4

3

2

1