

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date

Appr

-

RELEASED

3/11/15

D

D

C


C

B

B

A

A

**SPECIFICATIONS:**

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Clamp: Phosphor Bronze, Nickel plated

Wire guard: Stainless Steel

Electrical:

Operation voltage: 150 V

Current rating: 5 A

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min @ 500 VDC

Mechanical:

Wire range: 26-20 AWG, 0.5mm²

Wire strip length: 8mm

Environmental:

Lead free, RoHS compliant.



Poles: 02 thru 24

A = .098 [2.50] X No. of Positions

B = .098 [2.50] x No. of Spaces

C = .098 [2.50] X No. of Positions + .024 [0.60]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS

DATE

DRAWN

HR

3/11/15

CHECKED

NP

3/11/15

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

EURO BLOCK, .098 [2.50] PITCH

SIZE

X

PART NO.

EB2A-XX-M-V

REV.

-

REF: S00067C

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1