

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/4/14	
A		UPDATE DRAWING	9/3/20	AY/EY



SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Grey

Contact: Copper Alloy, Tin plated

Electrical:

Voltage rating: 300V

Current rating: 5A

Dielectric withstanding voltage: 1600V for 1 minute

Mechanical:

Wire range: 22~18 AWG

Strip length: 8-9 mm

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Poles: 01 thru 30P

A= .138 [3.50] x No. of Poles + .059 [1.50]

B= .138 [3.50] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

APPROVALS		DATE
DRAWN	AY	8/4/14
CHECKED	SY	8/4/14
APPROVED		

TITLE MINI TYPE, SIMPLE TYPE CAGE CLAMP TERMINAL BLOCKS, 3.50MM PITCH		
SIZE X	PART NO. EB59A-XX-A	REV. A
REF: S00067C	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1