





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/24/08	
A		REDRAWN	1/12/12	



RECOMMENDED PCB LAYOUT



Positions: 2 thru 24
A= .197 [5.00] x No. of Positions
B= .197 [5.00] x No. of Spaces

	Tolerance
2-6P	±.006 [0.15]
7-12P	±.008 [0.20]
13-18P	±.012 [0.30]
19-24P	±.016 [0.40]

SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL 94V-0³⁵ [0.90]

Insulator color: Green

Clamp: Brass, Nickel plated

Contact: Brass, Tin plated

Screw: Steel, M2.5/Zn plated

Electrical:

Operation voltage: 300 VAC

Current rating: 10 Amps

Withstanding Voltage: 1.6KV

Mechanical :

Solid wire(AWG): 12-22

Stranded wire(AWG): 12-22

Torque(Lb-In): 3.5

Wire strip length(mm): 6-7

Temperature Rating:

Operating temperature: -40°C to +115°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS

DATE

DRAWN

DY

7/24/08

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE

MODULAR EURO BLOCK, VERTICAL,
.197" [5.00] PITCH

SIZE

X

PART NO.

EBAC-XX-C

REV.

A

REF: S00007T

SCALE: NTS

SHEET 1 OF 1