





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/7/13	
A		UPDATED DRAWING	9/25/18	HR/DH



SECTION A-A



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:
Insulator: PA66, rated UL 94V-0
Insulator color: Green
Contact: Brass, Tin plated.
Electrical:
Operation voltage: 300 VAC max
Current rating: 15 Amps
Contact resistance: 20 mohms max
Insulation resistance: 500 Mohms min @ 500 VDC
Dielectric withstanding voltage: 2,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant.



Positions: 02 thru 24

A = .197 [5.00] x No. of Positions

B = .197 [5.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 ØX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS		DATE
DRAWN	AY	11/7/13
CHECKED	NP	11/7/13
APPROVED		

**ADAM
TECH**
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

EURO BLOCK, .197 [5.00] PITCH, VERTICAL

SIZE X	PART NO. EBPA-XX-C	REV. A
REF: S00067C	SCALE: NTS	SHEET 1 OF 1