

6

5

4

3

2





1

APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	6/13/14	
A		UPDATE SHAPE	10/27/14	AY/NP
B		ADDED SHAPE	12/22/16	AY/IC
C		UPDATE DRAWING	9/11/20	OW/CC

D

D



RECOMMENDED PCB LAYOUT



Positions: 02 thru 24
 A= .138 [3.50] x No. of Spaces + .169 [4.30]
 B= .138 [3.50] x No. of Spaces

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Copper Alloy, Tin plated

Electrical:

Voltage rating: 300 V

Current rating: 8 A

Dielectric withstanding voltage: 1600V for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

APPROVALS	DATE
DRAWN	AY
CHECKED	
APPROVED	

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE

TERMINAL BLOCK, STRAIGHT, .138" [3.50] PITCH

SIZE

X

PART NO.

EBRA-XX-A

REV.

C

REF:

S00067C

SCALE:

NTS

SHEET

1 OF 1

6

5

4

3

2

1