







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/18/19	
A		UPDATED DRAW	3/11/19	AY/TW



Bottom Cover and Terminal

FH-A-A01
(1) (2) (3)(4)

- (1). SERIES NO.
- (2). TYPE
- (3). CONTACT TYPE
A=.250" [6.35mm]
- (4). FUSE TYPE
01=5x20

SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL94V-0

Insulator color: Black (Top and Bottom)

Contact: Phosphor Bronze, Tin plated

Fuse: 5x20mm, 250V, 3 Amp

Temperature Rating:

Operating temperature: -20°C to +70°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	Ø.X ±.10
.XX ±.020	Ø.XX ±.015
.XXX ±.015	Ø.XXX ±.010

APPROVALS		DATE	
DRAWN	AY	1/18/19	
CHECKED	TW	1/18/19	
APPROVED			

ADAM TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
FUSE HOLDER, .250" QD
5X20 FUSE, 250V 3 Amp

SIZE X	PART NO. FH-A-A01B	REV. A
REF: S00181C	SCALE: NTS	SHEET 1 OF 1