







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/10/05	
A		REDRAWN	11/29/11	



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: SPCC

Clinch Nut: Brass, Nickel plated

Boardlock: Brass, Nickel plated

Screwlock: Brass, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant



HDTXX	DIMENSIONS											
	A		B		C		D		E		F	
15	.643	[16.33]	.984	[24.99]	1.213	[30.81]	.118	[2.29]	.045	[1.145]	.277	[7.04]
26	.971	[24.66]	1.312	[33.32]	1.541	[39.14]	.118	[2.29]	.045	[1.145]	.271	[6.88]
44	1.511	[38.38]	1.852	[47.04]	2.088	[53.04]	.118	[2.29]	.045	[1.145]	.271	[6.88]
62	2.159	[54.84]	2.500	[63.50]	2.729	[69.32]	.095	[2.41]	.047	[1.205]	.276	[7.00]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN

SS

5/10/05

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

HIGH DENSITY D-SUB SOCKET, R/A
#4-40 INSERTS & FORKED BOARDLOCKS

SIZE

X

PART NO.

HDLXX-SL-C

REV.

A

REF:

S00087T

SCALE:

NTS

SHEET 1 OF 1