





APPROVED: _____

DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-	7155	RELEASED	10/09/06	
A		REDRAWN	11/25/11	
B		ADDED DIM.	9/6/18	AY/TY



DETAIL A



DETAIL B



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Shield: Copper Alloy, Nickel Plated

Contacts: Copper Alloy

Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Copper underplate on tails

Electrical:

Current rating: 0.5 Amps max.

Contact resistance: 10 mohms max.

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 300 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ±.10 Ø.X ±.10
.XX ±.020 Ø.XX ±.015
.XXX ±.015 Ø.XXX ±.010

APPROVALS		DATE
DRAWN	BW	10/09/06
CHECKED		
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
HDMI CONNECTOR, RIGHT ANGLE,
SURFACE MOUNT

SIZE	PART NO.	REV.
X	HDMI-S-RA-TSMT	B
REF:	S00013T	SCALE: NTS
SHEET 1 OF 1		