




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/10/05	
A		ADDED .090 DIMENSION	02/12/08	BAS



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Steel, Tin plated

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -65°C to +125°C

Environmental:

Lead free, RoHS compliant



Unit: Inch / mm

Positions	DIMENSIONS			
	A	B	C	D
15	.666 [16.92]	.984 [24.99]	1.213 [30.81]	.759 [19.28]
26	.994 [25.25]	1.312 [33.32]	1.541 [39.14]	1.083 [27.51]
44	1.534 [38.96]	1.852 [47.04]	2.088 [53.04]	1.626 [41.30]
62	2.182 [55.43]	2.500 [63.50]	2.729 [69.32]	2.271 [57.70]
78	2.079 [52.81]	2.406 [61.11]	2.635 [66.93]	2.099 [55.32]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: HIGH DENSITY D-SUB PLUG, CRIMP & POKE
HDTXX-PR
ADDED .120 [3.05] MOUNTING HOLES

DRAWN	SS	5/10/05	SIZE	PART NO.	REV.
CHECKED			X	HDTXX-PR	A
APPROVED			REF:	SCALE: NTS	SHEET 1 OF 1