




Rev	AWO #	Description	Date	Appr
-		RELEASED	11/15/043	

APPROVED: _____

DATE: _____ TITLE: _____



Unit: Inch / mm

POSITIONS	Socket Dimensions			
	A	B	C	D
15	.643 (16.33)	.984 (24.99)	1.213 (30.81)	.759 (19.28)
26	.971 (24.66)	1.312 (33.32)	1.541 (39.14)	1.083 (27.51)
44	1.511 (38.38)	1.852 (47.04)	2.008 (53.04)	1.626 (41.30)
62	2.159 (54.84)	2.500 (63.50)	2.729 (69.32)	2.272 (57.71)

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: D-SUB,HIGH DENSITY, STRAIGHT
FEMALE SOLDER CUP

Plating: Gold Flash over Nickel underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 5 Amps max
Insulation resistance: 5000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC for 1 minute
Temperature Rating: Operating temperature: -65°C to +125°C

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 ØXX ± .10 .XX ± .020 ØXXX ± .015 .XXX ± .015 ØXXX ± .010				APPROVALS		DATE	
DRAWN	SS	11/15/04					
CHECKED							
APPROVED							

SIZE		PART NO.		REV.	
X		HDTXX-SD-JS		-	
REF:		SCALE: NTS		SHEET 1 OF 1	