


APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/11/05	
A		REDRAWN	10/8/12	



HDTXX	DIMENSIONS				
	A	B	C	D	E
15	.643 [16.33]	.984 [24.99]	1.213 [30.81]	.756 [19.20]	.090 [2.29]
26	.971 [24.66]	1.312 [33.32]	1.541 [39.14]	1.091 [27.70]	.090 [2.29]
44	1.511 [38.38]	1.852 [47.04]	2.088 [53.04]	1.618 [41.10]	.090 [2.29]
62	2.159 [54.84]	2.500 [63.50]	2.729 [69.32]	2.256 [57.30]	.095 [2.41]

SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Shell: Steel, Tin plated
Chinich Nut: Brass, Nickel plated
Screwlock: Brass, Nickel plated
Plating:
Gold flash over Nickel underplate overall
Electrical:
Insulation resistance: 1,000 Mohms min @500 VDC
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Environmental:
Lead free, RoHS compliant

ROHS
COMPLIANT

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

HIGH DENSITY D-SUB SOCKET
CRIMP & POKE, .120 [3.05] MOUNTING HOLES

APPROVALS		DATE		TITLE	
DRAWN	SS	5/11/05		HIGH DENSITY D-SUB SOCKET	
CHECKED				CRIMP & POKE, .120 [3.05] MOUNTING HOLES	
APPROVED					

SPECIFICATIONS:
Material:
Insulator: PBT, glass reinforced, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Shell: Steel, Tin plated
Chinich Nut: Brass, Nickel plated
Screwlock: Brass, Nickel plated
Plating:
Gold flash over Nickel underplate overall
Electrical:
Insulation resistance: 1,000 Mohms min @500 VDC
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Environmental:
Lead free, RoHS compliant

ROHS
COMPLIANT