




Rev	AWO #	Description	Date	Appr
-		RELEASED	11/6/07	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

G = Gold flash over Nickel underplate overall

T = Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 2 Amp max

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1

minute

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant

PLATING	ADAM TECH P/N:
GOLD	HMSA-G
TIN	HMSA-T

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES		ADAM TECH	
.X ± .10	ØX ± .10	909 Rahway Avenue, Union, NJ 07083	
.XX ± .020	ØXXX ± .015	Phone: 908-687-5000 Fax: 908-687-5710	
.XXX ± .015	ØXXX ± .010		
APPROVALS	DATE	TITLE .50 [1.27] MINI SHUNT, HANDLE TOP .216 [5.50] HEIGHT, COLOR BLACK	
DRAWN	SS	SIZE	
CHECKED		PART NO.	
APPROVED		HMSA-X	
REF:		SCALE: NTS	
		SHEET 1 OF 1	

ADAM TECH