

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/5/12	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi-Temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 300 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.

Positions: 06 thru 80
A= .050 [1.27] x No. of Positions + .009 [0.24]
B= .050 [1.27] x No. of Spoces
C= .050 [1.27] x No. of Positions - .100 [2.54]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]

TOLERANCES: EXCEPT AS NOTED

INCHES HOLES

.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS DATE

DRAWN AY 7/5/12

CHECKED LW 7/5/12

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

.050" RECEPTACLE STRIP, DUAL ROW, SMT

.085" INSULATOR HEIGHT, GOLD PLATED

A

B

C

D

A

B

C

D

6

5

4

3

2

1



SIZE	PART NO.	REV.
X	HRS-2C-XX-G-SMT-P	-