

6

5

4

3



2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/02/12	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi-Temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Copper underplate on SMT tails

Electrical:

Current rating: 1 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 300 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 06 thru 80
A = .050 [1.27] x No. of Positions + .009 [0.24]
B = .050 [1.27] x No. of Spoces
C = .050 [1.27] x No. of Positions - .100 [2.54]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.050" RECEPTACLE STRIP, DUAL ROW, SMT
.085" INSULATOR HEIGHT, SEL-GOLD PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				HOLES			
APPROVALS				DATE				DATE			
DRAWN	TW			10/02/12				10/02/12			
CHECKED	AY			10/02/12				10/02/12			
APPROVED											
TITLE				SIZE				PART NO.			
X				X				HRS-2C-XX-SG-SMT-P			
REF: S00032T				SCALE: NTS				SHEET 1 OF 1			