






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/17/05	
A		REDRAWN	9/19/11	
B		REDRAWN	4/30/13	
C		REDRAWN	12/31/13	AY/GC
D		UPDATE INSULATOR SPEC.	8/24/16	AY/CH
E		REMOVED TERMINAL OPTION #3	8/24/16	AY/CH
F		UPDATE DIM.	11/1/18	AY/SL



SECTION A-A



RECOMMENDED
 PANEL CUT-OUT

SPECIFICATIONS:

Material:
 Insulator: PA66, rated UL 94V-0
 Insulator color: Black
 Contact: Copper Alloy, Tin Plated
 Electrical:
 Rating: 15A @ 250V C-ULus
 10A @ 250V ENEC

Insulation resistance: 100 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 3000 VAC for 1 minute
 Environmental:
 Lead free, RoHS compliant.

TERMINAL OPTIONS	
-1 .187 Q.C.	-2 .250 Q.C.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
		TITLE IEC FEMALE OUTLET, PANEL MOUNT		SIZE X	
APPROVALS DRAWN SS CHECKED APPROVED		DATE 6/17/05		PART NO. IEC-B-X	
REF: S00087C		SCALE: NTS		SHEET 1 OF 1	