

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/17/05	
A		REDRAWN	12/13/13	AY



SECTION A-A

TERMINAL OPTIONS		
-1	-2	-3
.187 Q.C.	.250 Q.C.	.157 Solder

SPECIFICATIONS:

Material:
Insulator: PA66, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy
Plating:
Tin over Copper underplate overall
Electrical:
Current rating: C-ULus: 15A @ 250V
ENEC: 10A @ 250V
Insulation resistance: 100 Mohms min @ 500 VDC
Dielectric withstanding voltage: 3,000 VAC for 1 minute
Environmental:
Lead free, RoHS compliant



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES			TITLE		
.X ± .10	Ø.X	± .10	IEC FEMALE OUTLET		
.XX ± .020	Ø.XX	± .015	SNAP-IN PANEL MOUNT		
.XXX ± .015	Ø.XXX	± .010			
APPROVALS			DATE		
DRAWN	SS	6/17/05			
CHECKED					
APPROVED					
SIZE			PART NO.		
X			IEC-D-X		
REF:	S0087C	SCALE: NTS	SHEET 1 OF 1		