

6

5

4

3




2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/24/13	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass T=0.20mm

Shell: Stainless T=0.25mm Brass, Tin plated

Plating:

Gold Flash over Nickel on contact area,
Tin over Copper underplate on tails.

Electrical:

Contact resistance: 50 mohms max.

Insulation resistance: 50 Mohms min. @ 100 VDC

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -20°C to +85°C

Environmental:

Lead free, RoHS compliant.

**ADAM TECH**909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710TITLE: MICRO USB, TYPE AB, SINGLE PORT
VERTICAL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED							
INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015	.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXXX	± .010	.XXX	± .015	ØXXXX	± .010
APPROVALS				DATE			
DRAWN	AY		9/24/13	SIZE	PART NO.	MCR-AB-S-VT	REV.
CHECKED	EH		9/24/13	X			-
APPROVED				REF:	S00126T	SCALE: NTS	SHEET 1 OF 1

A

B

C

D

A

B

C

D

6

5

4

3

2

1